

prevention • monitoring • therapy • professional

Blood Pressure Monitor For Pregnant Women

Model: AU941 f





7 / 14 / 21 / 28 Day AM / PM Averaging

Tracking variations in blood pressure readings between morning and evening is important for physicians to better understand, diagnose and manage hypertensive patients or patients with other forms of heart diseases. Blood pressure changes throughout the day and is influenced by physical and mental factors, measurement conditions and time.

Real **f**uzzy Technology

Real Fuzzy Technology determines ideal cuff pressure based on one's systolic blood pressure and arm size. Users no longer need to pre-set the inflation level before measurement. The technology eliminates arm discomfort through unnecessary high inflation settings and also prevents inaccurate readings caused by erroneous cuff inflation levels.

- 7/14/21/28 day AM/PM Averaging
- Movement Detection
- Real Fuzzy Technology
- Hypertension Risk Indication (HRI)
- Irregular Heartbeat Detection (IHB)
- Average of last 3 readings
- 120 memories for 2-users with date and time indication
- Guest mode
- Latex-free patented universal cone cuff
- PC Link (Optional)
- Adaptor socket
- Lifetime Calibration
- Carrying bag









7/14/21/28 Day AM/PM Averaging



Detection

Luon





Irregular Hearbeat



last 120 memories for s 2-Users with Date and Time Indication



Universal Cone Cuff 24-40cm

Universal Cone Cuff



Lifetime Calibration







Clinically Validated

This blood pressure monitor has passed the criteria of the European Society of Hypertension by achieving all requirements and achieved the highest possible grade (A/A) according to the criteria of the British Hypertension Society. This monitor further complies with the standard required by the Association for the Advancement of Medical Instrumentation (AAMI).



Universal Cone cuff fits arm circumference 24~40cm (9.4"~15.7")
Other size cuffs available upon request

	Model	Qty per carton	Carton volume
	AU941f	12 pcs	0.061cbm/ctn
	QTY per 20'	QTY per 40'	QTY per 40'HQ
	5496 pcs	10980pcs	12744 pcs

Storage and Transportation Condition -10°C~60°C(14°F~140°F) 10%~90% RH, 700~1060 hPa